

Acrylics

- * Laird Plastics in Illinois are sending us three samples:
 - * A Tecacryl rod, ~ 4 feet in length and about ~ 1.5 inch in diameter
 - * Plexiglas GS sheet, 96 inch length, and about 20 inches wide
 - * Arkema brand UV-transmitting Plexiglas
- * The attenuation measurements on these acrylics will not converge on the time scale necessary for SBND
- * For SBND, we will go with UTran cast acrylic
- * Questions:
 - * Should they be 1 inch wide, or 6 cm, like protoDUNE bars?
 - * What kind of polish do we need on the edges?